





# Adapter ring







## Adapter ring

When fitting an actuator to a thermostatic valve, an adapter ring is normally needed to ensure a perfect fit.

Different valves will require different adapter rings. Our standard thermostatic valves, [LinFlow-A](#) (angled) and [LinFlow-S](#) (straight), should be used with a VA 64 adapter ring.

For applications where pressure independent control is needed, the Pettinaroli 91, 92 or 93 series should be selected, along with a VA 64 adapter ring.

LinFlow-A / LinFlow-S	VA 64	Article #
		686565
91/92/93 (H,L,VL)	VA 64	Article #
		686565

Type	Tread	Manufacturer	Colour	Picture	Article #
VA 64	M28 x 1,5	<ul style="list-style-type: none"> <li>Lindab LinFlow-A / LinFlow-S valves</li> <li>Pettinaroli 91/92/93 valve series</li> </ul>	white grey		686565
VA 80	M30 x 1,5	<ul style="list-style-type: none"> <li>Broen TTR/TTV valves</li> <li>MNG (new 98)</li> <li>Onda</li> <li>Oventrop M30x1,5 (from 97)</li> <li>Schlösser (from 93)</li> <li>Comap (M30x1,5)</li> <li>TA from 99</li> <li>Empur</li> <li>Böhnisch (SBK) (H) (from 98)</li> <li>Thermotechnik TT-i</li> <li>Landis&amp;Gyr</li> </ul>	white grey		642108
VA 50	M30 x 1,5	<ul style="list-style-type: none"> <li>Ballorex Dynamic</li> <li>Honeywell&amp;Braukmann</li> <li>Reich</li> <li>MNG (before 98)</li> <li>Böhnisch (SBK) (H) (before 98)</li> <li>Cazzaniga</li> </ul>	dark grey		642111
VA 10	M30 x 1,5	<ul style="list-style-type: none"> <li>Dumser</li> <li>Cronatherm</li> <li>Vescal</li> <li>KaMo</li> <li>Strawa (from 03 new fitting)</li> </ul>	light grey		682067
VA 39	M30 x 1,0	<ul style="list-style-type: none"> <li>Oventrop (M30 x 1)</li> </ul>	pure white		682071
VA 78		<ul style="list-style-type: none"> <li>Danfoss RA</li> </ul>	pure white		642107
VA 59		<ul style="list-style-type: none"> <li>Danfoss RAV/L</li> </ul>	light grey		642115
VA 54		<ul style="list-style-type: none"> <li>MMA FV</li> </ul>	blue		884092
VA 55H		<ul style="list-style-type: none"> <li>MMA FVX</li> </ul>	dark grey		642109